

地址：深圳市南山区科技园南环路29号留学生创业园一期7楼
网址：www.scr-ky.com
电话：86-755-88257873 86222168
传真：86-755-82034858

2 灵敏型单向可控硅

表 1-2-1 灵敏型单向可控硅

Part number	IT(RMS)	VDRM	IGT Max	VGT	IH	Package	Counterpart Model
	(A)	(V)	(mA)	(V)	(mA)		
KS8B60	8	600	0.9	0.8	5	TO-220B	MCR72
KS8D60	8	600	0.2	0.8	5	TO-252	MCR72
KS8D60/80	8	600/800	0.2	0.8	5	TO-252	TS820
KS8B60/80	8	600/800	0.2	0.8	5	TO-220B	TS820
KS6D60	6	600	0.12	0.8	5	TO-252	2P4M,C106D/M,BT151
KS6H60	6	600	0.12	0.8	5	TO-202	2P4M,C106D/M
KS6R60	6	600	0.12	0.8	5	TO-126	2P4M,C106D/M
KS6N60	6	600	0.12	0.8	5	TO-92	2P4M,C106D/M
KS4N60	4	600	0.2	0.8	5	TO-92	2P4M,X0205
KS1.5N60	1.5	600	0.15	0.8	3	TO-92	MCR22-6
KS1L60	1	600	0.15	0.8	3	SOT-89	BT169D,BT169G
KS1S60	1	600	0.15	0.8	3	SOT-23	BT169D,BT169G
KS1N60	1	600	0.2	0.8	3	TO-92	BT1690d,BT169G,P0111,X0605MA
KS08S60	0.8	600	0.2	0.8	3	SOT-23	MCR100-8
KS08N600	0.8	600	0.2	0.8	3	TO-92	MCR100-8
KS08S40	0.8	400	0.2	0.8	3	SOT-23	MCR100-6
KS08N40	0.8	400	0.2	0.8	3	TO-92	MCR100-6
KS08M60	8	600	0.2	0.8	5	SOT-23-3L	MCR100-8
KS08M40	8	400	0.2	0.8	5	SOT-23-3L	MCR100-6
KS06N40	6	400	0.2	0.8	0.8	TO-92	PCR606
KS04N40	4	400	0.2	0.8	0.8	TO-92	PCR406

更新日期：2019年8月2日星期五